

# DTU362AWK

Safety switch, double throw, non fusible, 60 A,  
600 VAC/VDC, 3 poles, 60 hp, NEMA 12, no  
knock outs



## Main

Product	Double Throw Safety Switch
Duty Rating	General duty
Disconnect Type	Non-fusible disconnect switch
Factory Installed Neutral	None
Number of Poles	3
Current Rating	60 A
Voltage Rating	600 V AC 600 V DC
Enclosure Rating	NEMA 12
Maximum Horse Power Rating	10 Hp 240 V at AC 50-60 Hz for 1 phase conforming to NEC 240.6 20 Hp 240 V at AC 50-60 Hz for 3 phase conforming to NEC 430.52 25 Hp 480 V at AC 50-60 Hz for 1 phase conforming to NEC 240.6 50 Hp 480 V at AC 50-60 Hz for 3 phase conforming to NEC 430.52 30 Hp 600 V at AC 50-60 Hz for 1 phase conforming to NEC 240.6 60 Hp 600 V at AC 50-60 Hz for 3 phase conforming to NEC 430.52 10 Hp 250 V at DC 30 hp 600 V at DC

## Complementary

Short-circuit current	10 KA H or K 200 kA R, J or T
Fuse type	H or K R, J or T
Mounting Type	Surface
Wire Size	AWG 12...AWG 2 aluminium AWG 14...AWG 2 copper
Tightening torque	35 Lbf.In (3.95 N.m) 0.00...0.01 in <sup>2</sup> (2.06...5.26 mm <sup>2</sup> ) (AWG 14...AWG 10) 40 Lbf.In (4.52 N.m) 0.01 in <sup>2</sup> (8.37 mm <sup>2</sup> ) (AWG 8) 45 Lbf.In (5.08 N.m) 0.02...0.03 in <sup>2</sup> (13.3...21.15 mm <sup>2</sup> ) (AWG 6...AWG 4) 50 lbf.in (5.65 N.m) 0.04...0.05 in <sup>2</sup> (26.67...33.62 mm <sup>2</sup> ) (AWG 3...AWG 2)
Depth	6.93 in (176.02 mm)
Width	11.96 in (303.78 mm)
Height	29.94 in (760.48 mm)
Net Weight	44.97 lb(US) (20.4 kg)

## Environment

Certifications	UL Listed
----------------	-----------

## Ordering and shipping details

Category	00134 - DT SWITCH,NEMA12
Discount Schedule	DE1
GTIN	00785901307747
Nbr. of units in pkg.	1
Package weight(Lbs)	45 lb(US) (20.41 kg)

Returnability	Yes
Country of origin	US

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	10.10 in (25.654 cm)
Package 1 width	12.30 in (31.242 cm)
Package 1 Length	32.60 in (82.804 cm)

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

### Contractual warranty

Warranty	18 months
----------	-----------