

## Product data sheet

### Characteristics

# HOMT3020CP

Tandem mini circuit breaker, Homeline, 1 x 1 pole at 30A, 1 x 1 pole at 20A, 120/240 VAC, 10 kA AIR, plug in mount



### Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	30 A 20 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number of Poles	1P
Short Circuit Current Rating	10 kA
Number of Spaces	1
Circuit Breaker Type	Tandem
Ratings	HACR rated
Electrical Connection	Box lugs
Wire Size	AWG 14...AWG 8 aluminium/copper)1
Type of packing	Consumer packaging

### Complementary

Tightening torque	35.40 lbf.in (4.0 N.m) 0.00...0.01 in <sup>2</sup> (2.5...6 mm <sup>2</sup> ) (AWG 14...AWG 8)
Height	3.13 in (79.50 mm)
Width	1 in (25.40 mm)
Depth	2.98 in (75.69 mm)

### Environment

Ambient air temperature for operation	104 °F (40 °C)
---------------------------------------	----------------

### Ordering and shipping details

Category	00046 - HOM/T 15-30A 1P; 15-60A 2P
Discount Schedule	DE3D
GTIN	00785901403852
Nbr. of units in pkg.	100
Package weight(Lbs)	100 lb(US) (45.36 kg)
Returnability	Yes
Country of origin	MX

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.00 in (2.54 cm)
Package 1 width	2.60 in (6.604 cm)
Package 1 Length	3.20 in (8.128 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	4.53 lb(US) (2.055 kg)
Package 2 Height	3.40 in (8.636 cm)
Package 2 width	2.60 in (6.604 cm)

Package 2 Length	10.20 in (25.908 cm)
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	46.35 lb(US) (21.024 kg)
Package 3 Height	11.00 in (27.94 cm)
Package 3 width	7.90 in (20.066 cm)
Package 3 Length	17.40 in (44.196 cm)

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>