



Main

Product	Double Throw Safety Switch
Duty Rating	General duty
Disconnect Type	Non-fusible disconnect switch
Factory Installed Neutral	Neutral (factory installed)
Number of Poles	2
Current Rating	200 A
Voltage Rating	240 V AC 250 V DC
Enclosure Rating	NEMA 1
Maximum Horse Power Rating	15 hp 240 V at AC for 1 phase conforming to NEC 240.6

Complementary

Short-circuit current	10 kA H or J
Fuse type	H or J
Mounting Type	Surface
Wire Size	AWG 6...300 kcmil copper or aluminium
Tightening torque	340 lbf.in (38.41 N.m) (AWG 6...300 kcmil)
Depth	9.75 in (247.65 mm)
Width	19.63 in (498.60 mm)
Height	30.88 in (784.35 mm)
Net Weight	49.82 lb(US) (22.6 kg)

Environment

Certifications	UL Listed
----------------	-----------

Ordering and shipping details

Category	00033 - DT SWITCH,NEMA1
Discount Schedule	DE1
GTIN	00785901017417
Nbr. of units in pkg.	1
Package weight(Lbs)	52 lb(US) (23.59 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	10.50 in (26.67 cm)
Package 1 width	17.90 in (45.466 cm)
Package 1 Length	31.80 in (80.772 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------