



### Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Resistance heater with fan and thermostat
Power range	400...550 W
Input voltage	230 V AC 50/60 Hz
Electrical connection	2 screw terminals 2.5 mm <sup>2</sup>

### Complementary

Operating position	Vertical
Ambient air temperature for operation	-40...158 °F (-40...70 °C)
Temperature setting range	32...140 °F (0...60 °C)
IP degree of protection	IP20
Product certifications	UL VDE
Height	5.91 in (150 mm)
Width	6.10 in (155 mm)
Depth	8.46 in (215 mm)
Condition of use	Air sealed enclosure Heaters must be installed with a thermal controller Electrical protection is needed
Fixing mode	By clips
Mounting support	35 mm DIN rail

### Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	00785901732662
Nbr. of units in pkg.	1
Package weight(Lbs)	2.26 lb(US) (1.03 kg)
Returnability	Yes
Country of origin	DE

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	5.91 in (15 cm)
Package 1 width	6.10 in (15.5 cm)
Package 1 Length	8.46 in (21.5 cm)

## Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------