



## Main

Range	PowerLogic
Product or component type	Remote display
Device application	Human-machine dialogue application
Range compatibility	PowerLogic PM8000 PowerLogic ION7400
Display type	Colour TFT LCD

## Complementary

Display resolution	320 x 240 pixels QVGA
Display size	3.5 inch
Information displayed	Energy consumption Voltage Power Harmonic distortion Frequency Current System alarm I/O status
Messages display capacity	Graphic objects (bargraph, button, light...)
Local signalling	Status LED Green) Alarm LED Red)
Control type	5 x push-button
Connector type	RJ45
Provided equipment	Mounting Hardware Cable 9.84 ft (3 m)
Mounting mode	Flush-mounted
Mounting support	Framework remote display
Width	3.78 in (96 mm)
Height	3.78 in (96 mm)
Projecting depth	1.06 in (27 mm)
Net Weight	10.58 oz (300 g)

## Environment

IP degree of protection	IP54 IEC 60529
Relative humidity	5...95 %
Operating altitude	0...9842.52 ft (0...3000 m)
Ambient air temperature for operation	-13...140 °F (-25...60 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)
Product certifications	IEC

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Ordering and shipping details

Category	09782 - POWERLOGIC PM8000 ACCESSORIES
Discount Schedule	PL1
GTIN	00785901624981
Nbr. of units in pkg.	1
Package weight(Lbs)	1.14 lb(US) (0.52 kg)
Returnability	Yes
Country of origin	CN

## Packing Units

Package 1 Height	1.77 in (45.000 mm)
Package 1 width	3.78 in (96.000 mm)
Package 1 Length	3.78 in (96.000 mm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.