

Product data sheet

Characteristics

T02EN13G7

NEMA Contactor, TeSys N, nonreversing, Size 3, 90A, 50HP at 460VAC, 3 pole, 3 phase, 120VAC 50/60Hz coil, open



Main

Product Type	Contacteur
Range	TeSys N
Contacteur Type	Non-reversing
NEMA Size	3
Motor Horsepower Rating HP	25 Hp 200 V AC 30 Hp 230 V AC 50 Hp 460 V AC 50 hp 575 V AC

Complementary

Rated Current	90 A
[Ue] Rated Operational Voltage	600 V AC
Network Phases	3 phase
Number of Poles	3P
Control Circuit	Common control circuit
Coil Voltage	120 V AC
Auxiliary Contact Composition	1 NO
Electrical Connection	Lugs ordered separately
Height	6.38 in (162.05 mm)
Width	6.44 in (163.58 mm)
Depth	6.68 in (169.67 mm)
Product Weight	8.90 lb(US) (4.04 kg)

Environmental

Product Certifications	UL Listed CSA
NEMA Degree of Protection	Not rated (open device)

Ordering and shipping details

Category	21197 - TESYS N CONTACTORS SIZES 3 - 7
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	CZ

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information