



Main

Range	TeSys
Product or component type	Rotary handle
Product compatibility	V5 V6
Handle colour	Red

Complementary

Handle front plate colour	Yellow
Rotary handle padlocking	1 to 3 padlocks 0.16...0.31 in (4...8 mm)
Marking	0 - 1
Fixing mode	Hole 0.22 in (5.5 mm)
Handle front plate dimension	90 x 90 mm
Height	3.54 in (90 mm)
Width	3.54 in (90 mm)

Environment

IP degree of protection	IP40
-------------------------	------


Ordering and shipping details

Category	21730 - V VARIO SWITCH
Discount Schedule	CP1
GTIN	00785901562016
Nbr. of units in pkg.	1
Package weight(Lbs)	0.28 lb(US) (0.13 kg)
Returnability	Yes
Country of origin	CZ

Packing Units

Package 1 Height	0.930 dm
Package 1 width	0.930 dm
Package 1 Length	0.670 dm

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------