



Main

Device short name	A
Product or component type	Circuit breaker

Complementary

Line Rated Current	800 A
Number of Poles	3P
Breaking capacity code	J
Electrical connection	I-Line connection line Lugs load
Tightening torque	442.54 Lbf.in (50 N.m) 0.15...0.37 in <sup>2</sup> (95...240 mm <sup>2</sup> ) (AWG 3/0...500 kcmil) 8.85...11.51 lbf.in (1.0...1.3 N.m)
Height	12.86 in (326.64 mm)
Width	8.27 in (210.06 mm)
Depth	8.05 in (204.47 mm)
Continuous current rating	100 %

Ordering and shipping details

Category	01210-PG,H,J,K,L,N I-LINE BREAKERS
Discount Schedule	DE2
GTIN	00785901455547
Package weight(Lbs)	32.00 lb(US) (14.515 kg)
Returnability	Yes
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
RECh Regulation	<a href="#">RECh Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

---

Circularity Profile	<a href="#">End Of Life Information</a>
PVC free	Yes

---

### Contractual warranty

---

Warranty	18 months
----------	-----------

---