

Product data sheet

Characteristics

8903SPO10V02

Contactor, Type S, multipole lighting,
mechanically held, 60A, 2 pole, 110/120VAC
50/60Hz coil, open style



Main

| | |
|---------|--------------------------------------|
| Product | Mechanically Held Lighting Contactor |
| Type | S |

Complementary

| | |
|-------------------------|----------------------------------|
| Control Circuit Voltage | 120 V AC 60 Hz 110 V AC 50 Hz |
| Current Rating | 60 A |
| Number of Poles | 2P |
| Control Units | No control units |
| Pilot Light | Without pilot light |
| Auxiliary Contacts | Without |
| Other Options | None |
| Electrical connection | Lugs |
| Height | 7.80 in (198 mm) |
| Depth | 5.24 in (133 mm) |
| Width | 4.61 in (117 mm) |

Environment

| | |
|------------------------|--------------------------------------|
| Enclosure Type | Not rated (open device) surface none |
| Product certifications | UL Listed CSA |


Ordering and shipping details

| | |
|-----------------------|--------------------------------|
| Category | 21324 - 8903 S (NOT S°C) MECH. |
| Discount Schedule | CP1 |
| GTIN | 00785901102472 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 8.81 lb(US) (4.00 kg) |
| Returnability | No |
| Country of origin | MX |

Packing Units

| | |
|------------------|----------------------|
| Package 1 Height | 8.80 in (22.352 cm) |
| Package 1 width | 8.50 in (21.590 cm) |
| Package 1 Length | 12.40 in (31.496 cm) |

Offer Sustainability

| | |
|---------------------------|--|
| California proposition 65 | WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov |
| EU RoHS Directive | Not compliant |
| China RoHS Regulation |  China RoHS Declaration |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|