

HC4286WP

HCP 42 INCH WIDE by 86 INCH HIGH TYPE3R/12 I-LINE PANELBOARD ENCLOSURE



Main

Range of product	I-Line
Product or component type	Enclosure
Device application	Panelboard
Device short name	HCP

Complementary

Line Rated Current	1200 A 400 A 800 A 600 A
Enclosure nominal width	42.01 in (1067 mm)
Enclosure nominal height	85.98 in (2184 mm)
Enclosure nominal depth	9.49 in (241 mm)
Net Weight	323.00 lb(US) (146.51 kg)

Environment

NEMA degree of protection	NEMA 3R/12
Standards	CSA UL

Ordering and shipping details

Category	00110 - RTA PANELBOARD BOXES - SPECIAL, 3R, ETC.
Discount Schedule	PE1A
GTIN	00785901077220
Nbr. of units in pkg.	1
Package weight(Lbs)	419 lb(US) (190.06 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	1.61 ft (0.490 m)
Package 1 width	3.58 ft (1.092 m)
Package 1 Length	7.50 ft (2.286 m)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------