



Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Resistance heater
Power range	100 W
Input voltage	110...250 V AC 50/60 Hz
Electrical connection	4 screw terminals 2.5 mm ²

Complementary

Operating position	Vertical
Ambient air temperature for operation	-40...158 °F (-40...70 °C)
IP degree of protection	IP20
Electrical insulation class	Class II
Product certifications	UL VDE
Material	Body: extruded aluminium Cover plastic
Height	External 5.91 in (150 mm)
Width	External 2.36 in (60 mm)
Depth	External 3.54 in (90 mm)
Condition of use	Electrical protection is needed Heaters must be installed with a thermal controller Air sealed enclosure
Fixing mode	By clips
Mounting support	35 mm DIN rail

Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	00785901279976
Nbr. of units in pkg.	1
Package weight(Lbs)	0.75 lb(US) (0.34 kg)
Returnability	Yes
Country of origin	ES

Packing Units

Package 1 Height	5.12 in (130.000 mm)
Package 1 width	2.76 in (70.000 mm)
Package 1 Length	3.94 in (100.000 mm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------