



Main

Range of product	9080G
Product Type	Terminal block
Localisation on Device	Standard
Color	Red
Quantity	Set of 50

Complementary

Voltage Rating	600 V AC/DC
Current Rating	30 A UL 30 A CSA
Wire Size	AWG 22...AWG 10 copper
Mounting Type	35 mm DIN rail 9080GH track
Certifications	UL recognized E60616 CCN XCFR2 CSA file 62144 class 6228 01 CE
Protection Type	Fingersafe DIN 57470
Electrical Connection	Zinc plated steel box lugs
Material	Nylon block Tin plated brass busbar
Ambient air temperature for operation	-40...257 °F (-40...125 °C)
Electrical Connection Tightening Torque	Lug zinc plated steel 7...8 lbf.in (0.79...0.90 N.m) : AWG 22...AWG 10 copper)
Height	1.82 in (46.23 mm)
Width	1.72 in (43.69 mm)
Depth	0.235 in (5.97 mm)
Density	51 per foot
Compatible End Barrier	GM6B

Ordering and shipping details

Category	21702 - 9080 G (NOT GCB)
Discount Schedule	CP5
GTIN	00785901743224
Nbr. of units in pkg.	50
Package weight(Lbs)	0.02 lb(US) (0.01 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	5.08 in (12.903 cm)
Package 1 width	2.00 in (5.080 cm)
Package 1 Length	12.90 in (32.774 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------