

Product data sheet

Characteristics

8538SBG12V02S

NEMA Combination Starter, Type S, 30A
fusible disconnect, Size 0, 18A, 3 HP at 240
VAC polyphase, 120 VAC coil, NEMA 1



Main

| | |
|----------------------|--------------------------|
| Product | Combination Starter |
| Type | S |
| Control Circuit Type | Separate control circuit |

Complementary

| | |
|-------------------------|--|
| Control Circuit Voltage | 110 V AC 50 Hz 120 V AC 60 Hz |
| Starter Type | Non reversing |
| Number of Poles | 3P |
| Horsepower Rating | 3 Hp 200 V AC, 3 phase 3 hp 230 V AC, 3 phase |
| Maximum Voltage Rating | 600 V AC |
| Control Units | No control units |
| Pilot Light | No indicator |
| Auxiliary Contacts | Without |
| Thermal overload type | Melting alloy 3 |
| Disconnect Type | Fusible disconnect switch H, 30 A |
| NEMA size | 0 |

Environment

| | |
|----------------|--|
| Enclosure Type | NEMA 1 painted sheet steel with external reset |
|----------------|--|

Ordering and shipping details

| | |
|-----------------------|------------------------------------|
| Category | 21212 - 8538,39SB(NOT S*R,S*T,S*W) |
| Discount Schedule | CP1 |
| GTIN | 00785901748182 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 34.92 lb(US) (15.84 kg) |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| | |
|------------------|----------------------|
| Package 1 Height | 10.80 in (27.432 cm) |
| Package 1 width | 13.00 in (33.020 cm) |
| Package 1 Length | 29.00 in (73.660 cm) |

Offer Sustainability

| | |
|---------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| EU RoHS Directive | Not compliant |
| China RoHS Regulation | China RoHS Declaration |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|