



RTV Silicone Sealant - Blue, 6.5 Wt Oz

No. 14057 | Item# 1004792 | Case# 1004791

Product Description	For general-purpose sealing, bonding, protecting and waterproofing applications. Blue formulation is designed as a heavy-duty industrial gasket sealant.
Applications	Sealing, bonding, protection & waterproofing in HVAC, electrical, construction, metal working, for filling gaps between mating parts, gearboxes, pumps, motors & for general gasket sealing.
Unit Package Description	8 Ounce Pressurized Tube with Select-a-BEAD® Nozzle
Brand	CRC
Generic Description 1	Blue Silicone Sealant
Net Fill	6.5 Wt Oz
UPC Code	078254140575
Unit Dimensions	11.5H x 1.75W x 2.5D in
Units Per Case	12
Case Dimensions	11.75H x 7.37W x 7.37D in
Cases Per Pallet	90
Case Weight	7 lbs
I 2 of 5 Code	30078254140576
Appearance	Blue Paste
Flash point (F)	>212°F
Flash point (C)	>100°C
Flammability Class - CPSC	None
Spec Gravity Concentrate	1.007
Plastic Safe	Yes
Evaporation Rate	Slow
Curing Time	24 Hours
Dielectric Strength	25 kV/mm
Working Temp (F)	-70 to 400°F
Working Temp (C)	-45 to 204.4°C
Viscosity @68 F cP	Not Determined

Last revised: 10/8/2019

Page 1 of 2



Chemical Solutions to Keep You Moving™

f t y + in • 800-272-8963 • crcindustries.com



Gap Fill	Not Applicable
Shear Strength Steel Nuts & Bolts	Not Applicable
Locking Strength	Not Applicable
Propellant	Nitrogen
Aerosol Flammability Level	I
DOT Proper Shipping Name	Aerosols, Non-Flammable, Limited Quantity
Military Specification Number	Meets requirements of Mil-A-46106A
Federal Specification Number	TT-S-00230-C, TT-S-001543A
VOC % (Consumer Product def)	<3.0
VOC g/L (Consumer Product def)	<31
VOC lbs/gal (Consumer Prod def)	<0.26
VOC Category	Sealant or Caulking Compound
Removal (How To)	Scraping or a gasket remover product

Last revised: 10/8/2019
Page 2 of 2