

RG317

194# PET SPECIALTY FILAMENT TAPE

INTERTAPE POLYMER GROUP TECHNICAL DATA SHEET

DESCRIPTION

2.0 mil polyester (PET) film combined with solvent-less pressure sensitive adhesive. Offers outstanding holding power to a variety of surfaces.

PRODUCT APPLICATION

Provides excellent adhesion and "stiffness" for L-Clip closure applications. Stain resistant and clean removal from various surfaces without filament de-lamination. Also for light bundling and tabbing applications.

GOVERNMENT COMPLIANCE

Complies with the Federal Food, Drug and Cosmetic Act, CFR Title 21, Subpart B, Par. 175.105 (covers the use of pressure-sensitive adhesives and tapes for 'indirect contact' food packaging).

STORAGE RECOMMENDATION

Store new stock behind current stock. Store in a clean, dry place. Temperature of 70°F (21°C) +/- 6°F, and 40% to 50% relative humidity are recommended.

SHelf LIFE

When stored under recommended conditions, converted rolls have an expected shelf life of up to one year from date of shipment. Jumbo rolls have the same expected shelf life, but it is recommended that they are converted within 6 months of date of shipment.



100 Paramount Drive, Suite 300 | Sarasota, FL 34232 | USA
Customer Service: 800.IPG.8273 | 800.474.8273
Tape Technical Service: 877.447.4832
www.itape.com | info@itape.com

PHYSICAL PROPERTIES

The following data are nominal values based on PSTC, ASTM and other standard test. The data should not be considered as specifications.

Backing	2.0 mil (50µ) PET Film
Adhesive	Synthetic Rubber/Resin
Reinforcement	Fiberglass
Adhesion to Steel (oz/in of width) ASTM D-3330 @ 90° Angle	71 (19.4 N/25mm)
Tensile Strength (lbs/in of width) ASTM D-3759	194 (849 N/25mm)
Elongation (% at break) ASTM D-3759	4
Operating Temperature Range	-25°F to +158°F -31°C to +70°C
Total Thickness (mils) ASTM D-3652	5.5 (0.14mm)
Color	Clear



While we believe them to be reliable, the statements and information herein are only for general guidance and are not warrants or guarantees for accuracy and completeness. The user must, by test or otherwise, determine suitability for this purpose. There is no warranty of fitness for a particular purpose. Our standard term and conditions of sale apply exclusively to all orders, and all liability for damages of any kind, including consequential, exceeding purchase price is excluded. No one is authorized by us to make oral warranties. We reserve the right to make changes without notice or obligation in our products and publications.

EFFECTIVE: 10/14

