



**Syntha-Tech? Lubricant with PTFE, 11 Wt Oz**  
 No. 03054 | Item# 1003310 | Case# 1003309

Product Description	NSF, H1 registered, zero VOC, unique blend of synthetic lubricants that utilizes PTFE, anti-wear and extreme pressure additives to provide unparalleled lubricating performance.
Applications	Bearings, gears, linkages, motors, chains, cables, rollers, guide bars, pulleys, cams, valves, ball joints, hinges, slides, cutting tools, taps, dies, pistons, handling equipment, conveyors, hoists, lifts, doors, fans, and processing equipment.
Unit Package Description	16 Ounce Aerosol
Brand	CRC
Generic Description 1	Synthetic Lubricant with Perma-Lock®
Net Fill	11 Wt Oz
UPC Code	078254030548
Unit Dimensions	7.75H x 2.63W x 2.63D in
Units Per Case	12
Case Dimensions	8.1H x 8.3W x 11.1D in
Cases Per Pallet	133
Case Weight	12 lbs
I 2 of 5 Code	30078254030549
Appearance	White Liquid
Base Type	Polyolefin
Flash point (F)	117 F
Flash point (C)	47 C
Flammability Class - CPSC	Flammable
Spec Gravity Concentrate	0.8
Plastic Safe	Safe on Most Plastics (Test small area)
Film Type	Synthetic
Film Thickness	Not Determined
Evaporation Rate	Slow

Last revised: 1/17/2020  
 Page 1 of 2





Dielectric Strength	32,480 Volts
Working Temp (F)	-40 to 450°F
Working Temp (C)	-40 to 232.2°C
Propellant	Carbon Dioxide
NSF Category Code	H1
NSF Number	142820
Aerosol Flammability Level	II
DOT Proper Shipping Name	Aerosols, flammable
VOC % (Consumer Product def)	98.1
VOC g/L (Consumer Product def)	40.2
VOC lbs/gal (Consumer Prod def)	0.34
VOC Category	Multi-Purpose Lubricant
Removal (How To)	Remove with degreaser

Last revised: 1/17/2020  
Page 2 of 2