

758

120# PAPER MEDIUM GRADE FILAMENT TAPE

INTERTAPE POLYMER GROUP® TECHNICAL DATA SHEET

DESCRIPTION

A natural colored crepe paper backed tape, laminated to uni-directional fiberglass filaments, and coated with "hot melt" applied synthetic rubber pressure-sensitive adhesive. The paper backing can be easily marked with pen, crayon, or rubber stamp. Provides excellent performance for medium duty general purpose applications where a paper backing is desirable.

PRODUCT APPLICATION

Medium duty bundling (plastic pipe, aluminum extrusions, carpet and vinyl flooring covering rolls), textile (beaming/leasing), packaging (Post Office and UPS acceptable), reinforcing & strapping, unitizing/palletizing, "Grading Tape" (meat packaging), dynamite tape (bundling sticks, fuses, caps, etc.).

NOMINAL VALUES

The following data are nominal values based on PSTC, ASTM and other standard test. The data should not be considered as specifications.

Backing	Crepe Paper
Adhesive	Synthetic Rubber/Resin
90° Adhesion to Steel (oz/in of width) PSTC-101	85 (23.3 N/25mm)
Tensile Strength (lbs/in of width) PSTC-131	120 (525 N/25mm)
Elongation (% at break) PSTC-133	5
Total Thickness (mils) PSTC-133	7.9 (0.20mm)
Color	Natural



100 Paramount Drive, Suite 300 | Sarasota, FL 34232 | USA
Customer Service: 800.IPG.8273 | 800.474.8273
Tape Technical Service: 877.447.4832
www.itape.com | info@itape.com

While we believe them to be reliable, the statements and information herein are only for general guidance and are not warrants or guarantees for accuracy and completeness. The user must, by test or otherwise, determine suitability for this purpose. There is no warranty of fitness for a particular purpose. Our standard term and conditions of sale apply exclusively to all orders, and all liability for damages of any kind, including consequential, exceeding purchase price is excluded. No one is authorized by us to make oral warranties. We reserve the right to make changes without notice or obligation in our products and publications.

EFFECTIVE: 09/22

