

RHT22 Temperature and Humidity Indicator

Dual display for simultaneous viewing of Temperature and Humidity

Features:

- For use in labs, green houses, cleanrooms, warehouses, museums, offices, schools, and homes
- Icons indicate comfortable, wet or dry humidity conditions
- Large, easy to read display is °F/°C switchable
- Min/Max with reset to monitor changing conditions
- Wall mount or built-in stand for desk mounting
- Complete with AAA battery
- Optional model complete with Certificate of Traceability to N.I.S.T.
- 1-year warranty

Applications:

Monitor Temperature and Humidity in virtually any indoor setting



NIST
TRACEABLE
CALIBRATION
AVAILABLE

Specifications

Humidity Range	10 to 99%RH
Humidity Accuracy	±5%RH
Humidity Resolution	1%RH
Temperature Range	32 to 122°F (0 to 50°C)
Temperature Accuracy	±2°F / 1°C
Temperature Resolution	0.2°F/0.1°C
Power	AAA battery
Dimensions/Weight	4.25 x 4 x 0.8" (110 x 102 x 20mm) / 5oz (142g)

Ordering Information:

RHT22 Temperature and Humidity Indicator
RHT22-NIST RHT22 Including Certificate of Traceability to N.I.S.T.

