

# RG400

## 110# BOPP UTILITY FILAMENT TAPE

# INTERTAPE POLYMER GROUP® TECHNICAL DATA SHEET

### DESCRIPTION

An economical fiberglass reinforced polypropylene film combined with an aggressive 'solventless' pressure-sensitive adhesive. Provides resistance to filament delamination and separation, excellent adhesion to corrugated cartons and outstanding holding power. Will hand break, no knives needed.

### PRODUCT APPLICATIONS

Designed for the majority of packaging, palletizing and unitizing applications.

### STORAGE RECOMMENDATION

Store new stock behind current stock. Store in a clean, dry place. Temperature of 70°F (21°C) +/- 6°F, and 40% to 50% relative humidity are recommended.

### SHELF LIFE

When stored under recommended conditions, converted rolls have an expected shelf life of up to one year from date of shipment. Jumbo rolls have the same expected shelf life, but it is recommended that they are converted within 6 months of date of shipment.



100 Paramount Drive, Suite 300 | Sarasota, FL 34232 | USA  
Customer Service: 800.IPG.8273 | 800.474.8273  
Tape Technical Service: 877.447.4832  
www.itape.com | info@itape.com

### NOMINAL VALUES

The following data are nominal values based on PSTC, ASTM and other standard tests. The data should not be considered as specifications.

<b>Backing</b>	1.1 mil (28μ) Biaxial Oriented PP Film
<b>Adhesive</b>	Synthetic Rubber/Resin
<b>Adhesion to Steel</b> (oz/in of width) (at 90° peel angle) PSTC-101	80 (21.9 N/25mm)
<b>Tensile Strength</b> (lbs/in of width) PSTC-131	110 (482 N/25mm)
<b>Elongation</b> (% at break) PSTC-131	3.5
<b>Total Thickness</b> (mils) PSTC-133	5 (0.127mm)
<b>Quick Stick</b> (oz/in of width)	
To Kraft	8 (2.2 N/25mm)
To Steel	51 (14 N/25mm)
<b>Shear to Kraft Paper</b> (hours) (1" x 1" x 1000 grams)	> 166
<b>Operating Temperature Range</b>	+32°F ~ +140°F (0°C ~ +60°C)
<b>Color</b>	Clear



While we believe them to be reliable, the statements and information herein are only for general guidance and are not warrants or guarantees for accuracy and completeness. The user must, by test or otherwise, determine suitability for this purpose. There is no warranty of fitness for a particular purpose. Our standard term and conditions of sale apply exclusively to all orders, and all liability for damages of any kind, including consequential, exceeding purchase price is excluded. No one is authorized by us to make oral warranties. We reserve the right to make changes without notice or obligation in our products and publications.

EFFECTIVE: 7/14

