

# PT5

## MULTI-SURFACE PAINTER'S TAPE

### DESCRIPTION

A crepe paper masking tape coated with a pressure-sensitive, rubber based adhesive for use on walls, trim, glass, metals and lacquered/varnished surfaces. Clean removal up to 24 hours

### PRODUCT APPLICATION

Designed for paint masking and other all-purpose applications. Can also be used for light-weight packaging, bundling, splicing and tabbing.

### STORAGE RECOMMENDATION

Store new stock behind current stock. Store in a clean, dry place. Temperature of 70°F (21°C) +/- 6°F, and 40% to 50% relative humidity are recommended.

### SHELF LIFE

When stored under recommended conditions, converted rolls have an expected shelf life of up to one (1) year from the date of shipment. Jumbo rolls have the same expected shelf life, but it is recommended that they are converted within six (6) months of date of shipment.



100 Paramount Drive, Suite 300 | Sarasota, FL 34232 | USA  
Customer Service: 800.IPG.8273 | 800.474.8273  
Tape Technical Service: 877.447.4832  
www.itape.com | info@itape.com

While we believe them to be reliable, the statements and information herein are only for general guidance and are not warrants or guarantees for accuracy and completeness. The user must, by test or otherwise, determine suitability for this purpose. There is no warranty of fitness for a particular purpose. Our standard term and conditions of sale apply exclusively to all orders, and all liability for damages of any kind, including consequential, exceeding purchase price is excluded. No one is authorized by us to make oral warranties. We reserve the right to make changes without notice or obligation in our products and publications.

EFFECTIVE: 10/15

## INTERTAPE POLYMER GROUP® TECHNICAL DATA SHEET

### NOMINAL VALUES

The following data are nominal values based on PSTC, ASTM and other standard tests. The data should not be considered as specifications.

<b>Backing</b>	Coarse Crepe
<b>Adhesive</b>	Synthetic Rubber/Resin
<b>Adhesion to Steel</b> (oz/in of width) PSTC-101	41 (11.2 N/25mm)
<b>Tensile Strength</b> (lbs/in of width) PSTC-131	25 (109 N/25mm)
<b>Elongation</b> (% at break) PSTC-131	10
<b>Total Thickness</b> (mils) PSTC-133	5.75 (0.146mm)
<b>Quick Stick to Steel</b> (oz/in of width) PSTC-5	17.8 (4.9 N/25mm)
<b>Quick Stick to Kraft</b> (oz/in of width) PSTC-5	3.8 (1.04 N/25mm)
<b>Application Temp. Range</b>	+50°F ~ +90°F (+10°C ~ +32°C)
<b>Operating Temp. Range</b>	+40°F ~ +150°F (+4°C ~ +66°C)
<b>Color</b>	Dark Blue

