

PE34

UV RESISTANT STUCCO MASKING TAPE

DESCRIPTION

PE34 has a durable, moisture resistant LDPE (polyethylene) backing with a rubber-based pressure-sensitive adhesive. Bonds well to a variety of surfaces and removes cleanly. Easy to unwind.

Designed to offer a high degree of conformability without excessive stretch. Stiffer backing makes it easier to handle in certain applications. UV resistance up to 30 days, depending upon conditions and surfaces.

PRODUCT APPLICATION

UV-resistant PE film tape is used to mask against overspray when applying stucco and EIFS, protecting surfaces such as windows, doors and frames. Can be used for seaming and sealing polysheeting and film indoors and outdoors where UV exposure is prevalent. Removes cleanly from most opaque surfaces up to 30 days.

SPECIFICATION CONFORMANCE

Tested in accordance with UL723 / ASTM E84



100 Paramount Drive, Suite 300 | Sarasota, FL 34232 | USA
Customer Service: 800.IPG.8273 | 800.474.8273
Tape Technical Service: 877.447.4832
www.itape.com | info@itape.com

While we believe them to be reliable, the statements and information herein are only for general guidance and are not warrants or guarantees for accuracy and completeness. The user must, by test or otherwise, determine suitability for this purpose. There is no warranty of fitness for a particular purpose. Our standard term and conditions of sale apply exclusively to all orders, and all liability for damages of any kind, including consequential, exceeding purchase price is excluded. No one is authorized by us to make oral warranties. We reserve the right to make changes without notice or obligation in our products and publications.

EFFECTIVE: 03/19

INTERTAPE POLYMER GROUP® TECHNICAL DATA SHEET

NOMINAL VALUES

The following data are nominal values based on PSTC, ASTM and other standard tests. The data should not be considered as specifications.

Backing	Polyethylene (PE) Film
Adhesive	Synthetic Rubber
Adhesion to Steel (oz/in of width) ASTM D3330	75 (20.5 N/25mm)
Tensile Strength (lbs./in of width) ASTM D3759	21 (92 N/25mm)
Total Thickness (mils) ASTM D3652	7.0 (0.178mm)
Elongation (% at break) ASTM D3652	75
Application Temperature Range	+45°F to +120°F (+7°C ~ +49°C)
Operating Temperature Range	+20°F ~ +200°F (-7°C ~ +93°C)
Color	Red, White

