

# Reinforced Construction Paper

## REINFORCED LAMINATED NATURAL KRAFT PAPER

# INTERTAPE POLYMER GROUP® TECHNICAL DATA SHEET

### DESCRIPTION

3-way fiberglass reinforced natural kraft paper.

### PRODUCT APPLICATION

Used as a protection for finished floors/surfaces during construction or remodeling/repair. Non-bleeding, non-staining. Skid and slip resistant. Water and oil resistant. Withstands medium to heavy foot traffic.

### CONSTRUCTION (PER 3,000 SQUARE FEET):

<b>Top Ply:</b>	30 lb Natural Kraft Paper (virgin fibers)
<b>Bottom Ply:</b>	30 lb Natural Kraft Paper (virgin fibers)
<b>Laminating Adhesive:</b>	14 lb High Melt Index Polypropylene Based Co-Polymer
<b>MD Reinforcement:</b>	(1-1-1-1) 110 Fiberglass on 15mm centers
<b>CD Reinforcement:</b>	(1-1-1) 150 Fiberglass on 1.25" centers at 37° angle
<b>Total Basis Weight:</b>	77 lb

### PHYSICAL PROPERTIES:

<b>Caliper</b> (mils):	6.3
<b>MD Tensile</b> (lbs/in):	74
<b>CMD Tensile</b> (lbs/in):	24



100 Paramount Drive, Suite 300 | Sarasota, FL 34232 | USA

Customer Service: 800.IPG.8273 | 800.474.8273

Tape Technical Service: 877.447.4832

www.itape.com | info@itape.com

While we believe them to be reliable, the statements and information herein are only for general guidance and are not warrants or guarantees for accuracy and completeness. The user must, by test or otherwise, determine suitability for this purpose. There is no warranty of fitness for a particular purpose. Our standard term and conditions of sale apply exclusively to all orders, and all liability for damages of any kind, including consequential, exceeding purchase price is excluded. No one is authorized by us to make oral warranties. We reserve the right to make changes without notice or obligation in our products and publications.

EFFECTIVE: 4/09