

COMMERCIAL

DESCRIPTION

- Metal construction with Chrome plated or Classic Brushed Nickel finish
- 1/2" IPS shanks
- Designed to be installed on 8" to 16" centers
- Supplied with vandal resistant screws and metal pop-up waste assembly or metal grid where indicated

OPERATION

- Lever style handles with hot and cold color indicators
- Hot side counterclockwise to open (clockwise to close)
- Cold side clockwise to open (counterclockwise to close)

FLOW

 Water usage is limited to these maximum flow rates as indicated by the corresponding product markings
1.2 gpm max (4.5L/min) at 60 psi

CARTRIDGE

- 1224 cartridge design
- Nonmetallic and stainless steel material


STANDARDS

- Third party certified to WaterSense,® ASME A112.18.1/CSA B125.1, and all applicable requirements referenced therein
- Certified to NSF 61/9 & 372
- Products marked with 1.2 gpm are compliant with California water efficiency regulations
- Complies with California Proposition 65 and with the Federal Safe Drinking Water Act
- ADA for lever handles

WARRANTY

· Warranted for 5 years against material or manufacturing defects

Specifications



Two-Handle Widespread Lavatory Faucet				
MODEL	FLOW (gpm)	DRAIN	FINISH	WATERSENSE CERTIFIED
8922	1.2	Metal	Chrome	х
8922CBN	1.2	Metal	CBN	х
8924	1.2	Grid	Chrome	х


CBN-Classic Brushed Nickel





See table above

NOTE: Spout designed to be installed through 1" min. dia. hole, valves install through 1-1/8" min. dia. hole



(DO NOT SCALE)