


**ER collet, ER 16, Nominal clamping  $\varnothing$  d: 3/32mm**

**Order data**

Order number	308920 3/32
GTIN	4062406103767
Item class	32Z

**Description**
**Version:**

Through hardened and ground. Polished.

**Note:**

The collet clamping  $\varnothing$  range is always up to 1 mm less than nominal, e.g.  $\varnothing$  10 – 9 mm, except for  $\varnothing$  1, 1.5 and 2 (where it is only 0.5 mm).

Collets ER16, ER25 and ER32 without a seal also available in inch sizes via the eShop.

Concentricity:  $\leq 10 \mu\text{m}$

Overall length L: 27.5 mm

**Technical description**

Adapter	ER 16
Standard	ISO 15488-B
Concentricity	$\leq 10 \mu\text{m}$
Type	426 E
External $\varnothing$ D	17 mm
Overall length L	27.5 mm
Type of product	Clamping head

