



ER collet, ER 25, Nominal clamping \varnothing d: 1/2 mm



Order data

Order number	308960 1/2
GTIN	4062406104009
Item class	32Z

Description

Version:

Through hardened and ground. Polished.

Note:

Collets ER16, ER25 and ER32 without a seal also available in inch sizes via the eShop.

The collet clamping \varnothing range is always up to 1 mm less than nominal, e.g. \varnothing 10 – 9 mm, except for \varnothing 1, 1.5 and 2 (where it is only 0.5 mm).

Concentricity: $\leq 10 \mu\text{m}$

Overall length L: 34 mm

Technical description

Adapter	ER 25
Standard	ISO 15488-B
Concentricity	$\leq 10 \mu\text{m}$
Type	430 E
External \varnothing D	26 mm
Overall length L	34 mm
Type of product	Clamping head

