



## Heavy all-steel high-performance clamp with special jaw anvil, Jaw capacity: 400 mm



### Order data

Order number	861320 400
GTIN	4045197775078
Item class	82C

### Description

#### Version:

Beam and fixed jaw made of bright steel section (special profile), tempered and electro-galvanised. Slide jaw made of steel, drop-forged, tempered, and electro-galvanised. Wear-resistant smooth-running steel spindle with trapezoidal thread. Long working life due to heat-resistant special pressure pad with sintered steel inlay. Spindle tempered and burnished with adjustable clamp handle.

Can tilt through 30°.

#### Application:

For heaviest duty clamping of workpieces in steel construction, blacksmith's shops, HGV bodywork, machine tool manufacture etc. The movable special jaw anvil permits clamping diagonal workpieces. **Maximum clamping pressure up to approx. 22000 N.**

Cross section of the slide rail: 40×20 mm

Throat: 175 mm

Weight: 6 kg

### Technical description

Cross section of the slide rail	40×20 mm
---------------------------------	----------

Weight	6 kg
Throat	175 mm
Jaw capacity	400 mm
Type of product	Clamp

---

## Accessories

Pressure plate Type GSV	861121 GSV
Pressure plate Type GSP	861121 GSP