

Garant**Centre drill set HSS-E No. 111050 in a case, Type: 10****Order data**

Order number	111055 10
GTIN	4045197797759
Item class	11A

Description**Version:**

Composed of centre drills DIN 333.

Content:

Centre drill No. 111050, 1 pc. each in size 0.75; 1; 1.5; 1.6; 2; 2.5; 3; 3.15; 4; 5.

Shank: Parallel shank to h7

Number of drills: 10

Technical description

Number of drills	10
Tool material	HSS E
Standard	DIN 333
Type	A
Tolerance nominal \varnothing	k12
Countersink angle	60°

Shank	Parallel shank to h7
Colour ring	without
Type of product	convex

Accessories

Centre drill HSS-E A Nominal Ø DC k12 4 mm	111050 4
Centre drill HSS-E A Nominal Ø DC k12 0,75 mm	111050 0,75
Centre drill HSS-E A Nominal Ø DC k12 1,5 mm	111050 1,5
Centre drill HSS-E A Nominal Ø DC k12 2 mm	111050 2
Centre drill HSS-E A Nominal Ø DC k12 2,5 mm	111050 2,5
Centre drill HSS-E A Nominal Ø DC k12 3 mm	111050 3
Centre drill HSS-E A Nominal Ø DC k12 1 mm	111050 1
Centre drill HSS-E A Nominal Ø DC k12 1,6 mm	111050 1,6
Centre drill HSS-E A Nominal Ø DC k12 3,15 mm	111050 3,15
Centre drill HSS-E A Nominal Ø DC k12 5 mm	111050 5