



Tap wrench, adjustable, Type: 3



Order data

Order number	148410 3
GTIN	4062406208202
Item class	12L

Description

Version:

With hardened jaws and steel grips. For use in confined spaces one steel handle can be unscrewed.

For **standard** use: Zinc die-cast body.

Standard: DIN 1814

Capacity □: 4.9 - 12 mm

for hand taps DIN 352: M5 – M20

for hand reamer Ø DIN 206: 6.5 - 15 mm

Overall length: 370 mm

Technical description

for hand reamer Ø DIN 206	6.5 - 15 mm
Overall length	370 mm
for hand taps DIN 352	M5 – M20
Capacity □	4.9 - 12 mm
Standard	DIN 1814
Type of product	Tap wrench