



Tap wrench, adjustable, Type: 1.1/2



Order data

| | |
|--------------|---------------|
| Order number | 148410 1.1/2 |
| GTIN | 4062406208189 |
| Item class | 12L |

Description

Version:

With hardened jaws and steel grips. For use in confined spaces one steel handle can be unscrewed.

For **standard** use: Zinc die-cast body.

Standard: DIN 1814

Capacity □: 2 - 8 mm

for hand taps DIN 352: M1 – M12

for hand reamer Ø DIN 206: 2.5 - 9.5 mm

Overall length: 175 mm

Technical description

| | |
|---------------------------|--------------|
| for hand reamer Ø DIN 206 | 2.5 - 9.5 mm |
| Capacity □ | 2 - 8 mm |
| Overall length | 175 mm |
| for hand taps DIN 352 | M1 – M12 |
| Standard | DIN 1814 |
| Type of product | Tap wrench |