

**Garant**
**Double open ended spanner, Jaw widths: 10X11 mm**

**Order data**

Order number	610600 10X11
GTIN	4062406220204
Item class	61A

**Description**
**Version:**

Drop-forged. With close tolerance jaw widths.

With optimised profile shank for specially secure grip and ergonomic working. Exceptional tool life and wear resistance.

**Standard:**

**DIN 3110 / ISO 3318**

**Material:**

Chrome vanadium steel, non-flaking, matt chrome-plated.

Spanner length L: 155 mm

maximum jaw width b1: 24 mm

maximum jaw width b2: 27 mm

maximum jaw height h: 5 mm

**Technical description**

Spanner length L	155 mm
Width across flats	metric
Width across flats 1	10 mm
maximum jaw width b1	24 mm
Width across flats 2	11 mm
maximum jaw width b2	27 mm
maximum jaw height h	5 mm
Standard	DIN 3110

Standard	ISO 3318
Jaw position 1	15 °
Jaw position 2	15 °
Material	Chrome vanadium steel
Surface	matt chrome-plated
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner