

Garant
Double open ended spanner, Jaw widths: 5,5X7 mm

Order data

Order number	610600 5,5X7
GTIN	4062406220150
Item class	61A

Description
Version:

Drop-forged. With close tolerance jaw widths.

With optimised profile shank for specially secure grip and ergonomic working. Exceptional tool life and wear resistance.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome vanadium steel, non-flaking, matt chrome-plated.

Spanner length L: 120 mm

maximum jaw width b1: 15 mm

maximum jaw width b2: 17 mm

maximum jaw height h: 4 mm

Technical description

maximum jaw height h	4 mm
Spanner length L	120 mm
Width across flats 2	7 mm
maximum jaw width b2	17 mm
Width across flats 1	5.5 mm
maximum jaw width b1	15 mm
Width across flats	metric
Standard	DIN 3110

Standard	ISO 3318
Jaw position 1	15 °
Jaw position 2	15 °
Material	Chrome vanadium steel
Surface	matt chrome-plated
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner