

**Garant**
**Double open ended spanner, Jaw widths: 22X24 mm**

**Order data**

Order number	610600 22X24
GTIN	4062406220396
Item class	61A

**Description**
**Version:**

Drop-forged. With close tolerance jaw widths.

With optimised profile shank for specially secure grip and ergonomic working. Exceptional tool life and wear resistance.

**Standard:**

**DIN 3110 / ISO 3318**

**Material:**

Chrome vanadium steel, non-flaking, matt chrome-plated.

Spanner length L: 250 mm

maximum jaw width b1: 49 mm

maximum jaw width b2: 53 mm

maximum jaw height h: 8 mm

**Technical description**

Width across flats 2	24 mm
Width across flats 1	22 mm
maximum jaw width b1	49 mm
Spanner length L	250 mm
maximum jaw height h	8 mm
maximum jaw width b2	53 mm
Width across flats	metric
Standard	DIN 3110

Standard	ISO 3318
Jaw position 1	15 °
Jaw position 2	15 °
Material	Chrome vanadium steel
Surface	matt chrome-plated
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner