

Garant
Double open ended spanner, Jaw widths: 18X19 mm

Order data

Order number	610600 18X19
GTIN	4062406220327
Item class	61A

Description
Version:

Drop-forged. With close tolerance jaw widths.

With optimised profile shank for specially secure grip and ergonomic working. Exceptional tool life and wear resistance.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome vanadium steel, non-flaking, matt chrome-plated.

Spanner length L: 220 mm

maximum jaw width b1: 40 mm

maximum jaw width b2: 43 mm

maximum jaw height h: 7 mm

Technical description

Width across flats	metric
Spanner length L	220 mm
Width across flats 1	18 mm
maximum jaw width b2	43 mm
maximum jaw height h	7 mm
maximum jaw width b1	40 mm
Width across flats 2	19 mm
Standard	DIN 3110

Standard	ISO 3318
Jaw position 1	15 °
Jaw position 2	15 °
Material	Chrome vanadium steel
Surface	matt chrome-plated
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner