

**Garant****Abrasive cloth (A) robust, highly flexible, 230×280 mm, Grit: 320****Order data**

Order number	556790 320
GTIN	4045197808011
Item class	51E

**Description****Version:**

Densely woven, robust and **highly flexible** cotton fabric (resistant to oil and petroleum) evenly spread with synthetic resin bonded **standard aluminium oxide (A)**. Moulds ideally to the workpiece geometry. **No fraying, very high performance and long working life**. Sheet size 230×280 mm.

Very **sturdy and highly flexible abrasive cloth** (resistant to oil and petroleum). Moulds itself ideally to the workpiece geometry. Can be torn in longitudinal direction to yield clean edges along the weave without fraying.

**Application:**

Universally applicable, primarily for rubbing down by hand (for rubber sanding block see No. 557600).

Grinding medium code: A

Grit designation: very fine

**Technical description**

Grit	320
Grit designation	very fine
Grinding media	Aluminium oxide
Grinding medium code	A
Sanding disc width	280 mm

Sanding disc length	230 mm
Product name attribute	230×280 mm
Type of product	Abrasive cloth

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable only under restricted conditions		
Uni	suitable		
dry	suitable		

## Accessories

Steel backing plate	556950
Rubber sanding block	557600