

Garant GRIDLINE

## Roller cabinet with drawers 75 kg, 26×20G, Height mm / number of drawers: 885/5



### Order data

|              |               |
|--------------|---------------|
| Order number | 930615 885/5  |
| GTIN         | 4062406348755 |
| Item class   | 9GK           |

### Description

#### NOTE: Colour selection possible

#### Version:

#### Complete with drawers 26×20G.

Roller cabinet in 30×24G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With anti-roll lip on 4 sides, ribbed rubber mat and 2-component Haptoprene® push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

**100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport.

Absolutely necessary for all roller cabinets.

#### Fitted with:

Drawer front height, mm: 75, 75, 100, 150, 200

#### Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer/pull-out shelf load capacity: 75 kg

Drawer runner extension (partial/full extension): 100 %

Individual drawer release system: One-hand

Drawer usable area in G: 26×20

Height: 885 mm

Width: 750 mm

Depth: 600 mm

Usable height: 600 mm

Drawer body height: 700 mm

Drawer body usable height: 600 mm

## Technical description

|  |          |
|--|----------|
| Individual drawer release system                 | One-hand |
| Number of drawers                                | 5        |
| Usable height                                    | 600 mm   |
| Drawer body height                               | 700 mm   |
| Number of fixed wheels without parking brake     | 2        |
| Drawer runner extension (partial/full extension) | 100 %    |
| Drawer body usable height                        | 600 mm   |
| Treadless tyres                                  | yes      |
| Drawer usable area in G                          | 26×20    |
| Drawer usable depth in G                         | 20       |
| Drawer/pull-out shelf load capacity              | 75 kg    |
| Depth  | 600 mm   |
| Drawer usable width                              | 650 mm   |
| Number of doors                                  | 0        |
| Weight   | 106 kg   |
| Drawer usable depth                              | 500 mm   |
| with anti-roll lip                               | yes      |
| Drawer usable width in G                         | 26       |
| Width  | 750 mm   |
| Height   | 885 mm   |
| ComfortClose                                     | no       |
| Number of castors with parking brake             | 2        |

|  |  |
|--|--|
| maximum load capacity                        | 600 kg   |
| Electronic locking system can be retrofitted | yes  |
| Version                                      | wheeled  |
| Version                                      | with drawers   |
| Usable height for drawers                    | 600 mm   |
| Casing open at the top                       | no   |
| Number of pull-out shelves                   | 0  |
| Material thickness                           | 1.2 mm   |
| Drawer runner extension                      | Anti-tilt lock   |
| Height adjustment interval                   | 25 mm  |
| Cylinder lock                                | modular barrel   |
| Colour selection                             | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Product name attribute                       | 26x20G   |

## Accessories

|   |              |
|---|--------------|
| Drawer with one-handed individual drawer release system, 75 kg Drawer front height 150 mm | 930634 150   |
| Lock plate for GridLine Type HU21   | 914227 HU21  |
| Drawer with one-handed individual drawer release system, 75 kg Drawer front height 75 mm  | 930634 75    |
| Drawer with one-handed individual drawer release system, 75 kg Drawer front height 100 mm | 930634 100   |
| Drawer with one-handed individual drawer release system, 75 kg Drawer front height 200 mm | 930634 200   |
| Roller cabinet for drawers Height mm / number of drawers 885/0                            | 930617 885/0 |
| Sheet metal cover top with anti-roll lip on 4 sides Dimension in G 30X24                  | 951972 30X24 |
| Handle end caps 20 pieces Type 10   | 951025 10    |

