

Garant GRIDLINE

Roller cabinet with drawers 75 kg, 46×24G, Height mm / number of drawers: 885/6



Order data

Order number	931425 885/6
GTIN	4062406355418
Item class	9GK

Description

NOTE: Colour selection possible

Version:

Complete with drawers 46×24G.

Roller cabinet in 50×28G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With anti-roll lip on 4 sides, ribbed rubber mat and 2-component Haptoprene® push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

100% full extension drawers with differential runners. Drawers with slots at 50-mm/2G intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport.

Absolutely necessary for all roller cabinets.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Only GridLine divider inserts can be used in the widths 2G, 4G, 6G, 8G, 10G or 12 G.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer/pull-out shelf load capacity: 75 kg

Drawer runner extension (partial/full extension): 100 %

Individual drawer release system: One-hand

Drawer usable area in G: 46×24

Height: 885 mm

Width: 1250 mm
 Depth: 700 mm
 Usable height: 600 mm
 Drawer body height: 700 mm
 Drawer body usable height: 600 mm

Technical description

Individual drawer release system	One-hand
Drawer usable depth	600 mm
Drawer usable depth in G	24
Wheel Ø	125 mm
Number of fixed wheels without parking brake	2
Drawer usable width	1150 mm
Drawer/pull-out shelf load capacity	75 kg
Treadless tyres	yes
Number of doors	0
ComfortClose	no
Height	885 mm
Number of castors with parking brake	2
Drawer body height	700 mm
maximum load capacity	600 kg
with anti-roll lip	yes
Drawer body usable height	600 mm
Number of drawers	6
Drawer usable width in G	46
Drawer usable area in G	46×24
Drawer runner extension (partial/full extension)	100 %
Width	1250 mm
Electronic locking system can be retrofitted	yes
Depth	700 mm
Weight	182 kg

Usable height	600 mm
Version	wheeled
Version	with drawers
Casing open at the top	no
Usable height for drawers	600 mm
Number of pull-out shelves	0
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	46x24G

Accessories

Drawer with one-handed individual drawer release system, 75 kg Drawer front height 100 mm	931454 100
Lock plate for GridLine Type HU21	914227 HU21
Drawer with one-handed individual drawer release system, 75 kg Drawer front height 75 mm	931454 75
Roller cabinet for drawers Height mm / number of drawers 885/0	931427 885/0
Sheet metal cover top with anti-roll lip on 4 sides Dimension in G 50X28	951972 50X28