



Interchangeable one-hand clamp, Jaw capacity: 300mm



Order data

Order number	860286 300
GTIN	4062406276591
Item class	82C

Description

Version:

Ergonomically shaped 2-component plastic handle, burnished rail of drawn steel. **No tools required** for conversion to spreading, thanks to intelligent release mechanism in the upper part, **reversible**. With release handle for quick adjustment.

Application:

General purpose use, easy to use one-handed for clamping pressures (up to 2000 N).

Cross section of the slide rail: 20×6 mm

Spreading width: 200 - 565 mm

Throat: 90 mm

Technical description

Spreading width	200 - 565 mm
Jaw capacity	300 mm
Throat	90 mm
Cross section of the slide rail	20×6 mm
Type of product	Clamp

