Garant

Abrasive fleece pad, 158×224 mm, Fleece structure: 100



Order data

Order number	555995 100
GTIN	4062406300814
Item class	51M

Description

Version:

Synthetic nylon fleece impregnated with abrasive grit in synthetic resin bonding. High-performance fleece with **extremely dense grit distribution** deep into the fibres of the material. The special type of fleece structure permits **aggressive grinding characteristics**, a very long working life without clogging and an even **more uniform finish**.

Advantage:

- · Adapts to the component shape.
- · The open structure prevents clogging and reduces heat development.
- Even and reproducible finish.
- · Can be used wet or dry.
- · Contains no materials that could cause corrosion.

Application:

Can be used by hand, on hand block No. 556020 or on an orbital sander. **Coarse and aggressive:** removes rust, rust film, and surface soiling. For roughening old paint, varnish, plastics, rubber parts (e. g. prior to bonding).

Iron, sulphur and chlorine constituents: < 0.1 % Grit equivalent: 180 - 220 Grit designation: coarse Version: A Medium

Colour: red

Technical description

Grit equivalent

180 - 220

Version	A Medium	
Grit designation	coarse	
Colour	red	
Fleece structure	100	
Iron, sulphur and chlorine constituents	< 0.1 %	
Width	158 mm	
Length	224 mm	
Product name attribute	158×224 mm	
Type of product	Abrasive fleece pad	

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Stone	suitable only under restricted conditions		
Paint	suitable		
Uni	suitable		
wet maximum	suitable only under restricted conditions		

© Hoffmann GmbH Qualitätswerkzeuge

dry	suitable	
Accessories		
Hand block		556020
Mandrel		556030