

**Garant****Abrasive fleece pad, 158×224 mm, Fleece structure: 280****Order data**

Order number	555995 280
GTIN	4062406300838
Item class	51M

**Description****Version:**

Synthetic nylon fleece impregnated with abrasive grit in synthetic resin bonding. High-performance fleece with **extremely dense grit distribution** deep into the fibres of the material. The special type of fleece structure permits **aggressive grinding characteristics**, a very long working life without clogging and an even **more uniform finish**.

**Advantage:**

- **Adapts to the component shape.**
- **The open structure prevents clogging and reduces heat development.**
- **Even and reproducible finish.**
- **Can be used wet or dry.**
- **Contains no materials that could cause corrosion.**

**Application:**

Can be used by hand, on hand block No. 556020 or on an orbital sander. **Medium / medium fine:** Can be used universally for removing rust film, light soiling, discolouration; for rubbing down ground or brushed surfaces, or for degreasing and cleaning prior to painting.

Iron, sulphur and chlorine constituents: < 0.1 %

Grit equivalent: 280 - 360

Grit designation: medium fine

Version: A Very Fine

Colour: red

**Technical description**

Colour	red
--------	-----

Grit designation	medium fine
Fleece structure	280
Grit equivalent	280 - 360
Version	A Very Fine
Iron, sulphur and chlorine constituents	< 0.1 %
Width	158 mm
Length	224 mm
Product name attribute	158x224 mm
Type of product	Abrasive fleece pad

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Stone	suitable only under restricted conditions		
Paint	suitable		
Uni	suitable		
wet maximum	suitable only under restricted conditions		

dry

suitable

---

**Accessories**

Hand block

556020

Mandrel

556030