Garant

Roll of abrasive fleece, 115 mm \times 10 m, Fleece structure: 400



Order data

Order number	556087 400
GTIN	4062406300890
Item class	51M

Description

Version:

Synthetic nylon fleece impregnated with abrasive grit in synthetic resin bonding. High-performance fleece with **extremely dense grit distribution** deep into the fibres of the material. The special type of fleece structure permits **aggressive grinding characteristics**, a very long working life without clogging and an even **more uniform finish**.

Advantage:

- · Adapts to the component shape.
- $\cdot\,$ The open structure prevents clogging and reduces heat development.
- Even and reproducible finish.
- Can be used wet or dry.
- $\cdot\,$ Contains no materials that could cause corrosion.

Application:

Can be used by hand, on hand block No. 556020 or on an orbital sander. **Fine / very fine:** for cleaning delicate surfaces, for removing light scratches on metals. Also suitable for applying fine / very fine matt finishes to steels and non-ferrous metals.

Iron, sulphur and chlorine constituents: < 0.1 %

Grit equivalent: 400 - 600

Grit designation: fine

Version: S Super Fine

Colour: grey

© Hoffmann GmbH Qualitätswerkzeuge

Technical description

Grit equivalent	400 - 600	
Version	S Super Fine	
Colour	grey	
Grit designation	fine	
Fleece structure	400	
Iron, sulphur and chlorine constituents	< 0.1 %	
Roller width	115 mm	
Roll length	10 m	
Product name attribute	115 mm × 10 m	
Type of product	Roll of abrasive fleece	

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Stone	suitable only under restricted conditions		

© Hoffmann GmbH Qualitätswerkzeuge

Paint	suitable	
Uni	suitable	
wet maximum	suitable only under restricted conditions	
dry	suitable	

Accessories

Hand block	556020
Mandrel	556030