

Garant
Hand deburrer 90°, External Ø: 12,4mm

Order data

Order number	150400 12,4
GTIN	4045197087072
Item class	11M

Description
Version:

Three-flute countersink with ergonomic plastic handle. Handy power grip made of particularly tough and impact-resistant polypropylene. Due to its special surface structure, the **grip is non-slip even with oily or wet hands.**

Note:

For clean deburring and chamfering of holes.

Especially useful for assembly work.

For other hand deburrers, see Group 83.

Tool material: HSS

Number of cutting edges Z: 3

smallest countersink Ø for holes from: 2.8 mm

Overall length: 123 mm

Length of handle: 100 mm

Technical description

External Ø	12.4 mm
Length of handle	100 mm
smallest countersink Ø for holes from	2.8 mm
Overall length	123 mm
Number of cutting edges Z	3
Countersink tip angle	90°
Tool material	HSS

Colour ring	without
Type of product	Stepped drill and countersink

User data

	Suitability	V _c	ISO code
Alu plastics	suitable		
Aluminium (short chipping)	suitable		
Alu > 10% Si	suitable		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Steel < 900 N/mm ²	suitable only under restricted conditions		
INOX < 900 N/mm ²	suitable only under restricted conditions		
Ti > 850 N/mm ²	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
CuZn	suitable		
Uni	suitable		
dry	suitable		