



ER collet, ER 16, Nominal clamping \varnothing d: 7mm



Order data

Order number	308920 7
GTIN	4045197151162
Item class	32Z

Description

Version:

Through hardened and ground. Polished.

Note:

The collet clamping \varnothing range is always up to 1 mm less than nominal, e.g. \varnothing 10 – 9 mm, except for \varnothing 1, 1.5 and 2 (where it is only 0.5 mm).

Collets ER16, ER25 and ER32 without a seal also available in inch sizes via the eShop.

Concentricity: $\leq 10 \mu\text{m}$

Overall length L: 27.5 mm

Technical description

Nominal clamping \varnothing d	7 mm
Adapter	ER 16
Standard	ISO 15488-B
Concentricity	$\leq 10 \mu\text{m}$
Type	426 E
External \varnothing D	17 mm
Overall length L	27.5 mm
Type of product	Clamping head

