



ER collet, ER 32, Nominal clamping \varnothing d: 5 mm



Order data

| | |
|--------------|---------------|
| Order number | 309000 5 |
| GTIN | 4045197151506 |
| Item class | 32Z |

Description

Version:

Through hardened and ground. Polished.

Note:

Collets ER16, ER25 and ER32 without a seal also available in inch sizes via the eShop.

The collet clamping \varnothing range is always up to 1 mm less than nominal, e.g. \varnothing 10 – 9 mm, except for \varnothing 1, 1.5 and 2 (where it is only 0.5 mm).

Concentricity: $\leq 10 \mu\text{m}$

Overall length L: 40 mm

Technical description

| | |
|----------------------------------|-----------------------|
| Nominal clamping \varnothing d | 5 mm |
| Adapter | ER 32 |
| Standard | ISO 15488-B |
| Concentricity | $\leq 10 \mu\text{m}$ |
| Type | 470 E |
| External \varnothing D | 33 mm |
| Overall length L | 40 mm |
| Type of product | Clamping head |

