

**Feeler gauge, steel, T2, Number of blades: 13****Order data**

Order number	478200 13
GTIN	4045197207463
Item class	42H

Description**Version:**

Hard spring steel blades, clearly labelled. Equal width steel blades, pivoted on a riveted joint to fold away. Tapered steel blades. In nickel-plated casing, with clamp.

Steel feeler gauge, accuracy class T2. **Feeler gauge.**

Standard: Works standard

Blade thicknesses: 0.05 - 0.25 (0.05 increments) 0.3 -1.0 (0.1 increments) mm

Blade length: 100 mm

Technical description

Number of blades	13
Blade length	100 mm
Blade thicknesses	0.05 - 0.25 (0.05 increments) 0.3 -1.0 (0.1 increments) mm
Standard	Works standard
Tolerance	T3
Accuracy	T2
Material	Steel

Type of product

Thickness gauge

Services

Labelling laser-etched Type

018940