



Feeler gauge, steel, T3, Number of blades: 32



Order data

Order number	478100 32
GTIN	4045197437266
Item class	42H

Description

Version:

Hard spring steel blades, clearly labelled. Equal width steel blades, pivoted on a riveted joint to fold away. Tapered steel blades. In nickel-plated casing, with clamp.

Steel feeler gauge, ground, accuracy T3. **Feeler gauge.**

Standard: Works standard

Blade thicknesses: 0.03-0.10 (0.01 increments) 0.10-1.0 (0.05 increments) 0.125; 0.18; 0.23; 0.28; 0.32; 0.075 mm

Blade length: 100 mm

Technical description

Number of blades	32
Blade length	100 mm
Blade thicknesses	0.03-0.10 (0.01 increments) 0.10-1.0 (0.05 increments) 0.125; 0.18; 0.23; 0.28; 0.32; 0.075 mm
Standard	Works standard
Tolerance	T3

Accuracy	T3
Material	Steel
Type of product	Thickness gauge