



Try square Accuracy class 2, Stock length: 150X100mm



Order data

Order number	452600 150X100
GTIN	4045197205780
Item class	42F

Description

Version:

All faces and edges ground. Inspection test faces ground.

Application:

For accurate general workshop work.

Accuracy:

DIN 875 / 2 – angle tolerance e.g. for size 100×70 = 0.030 mm.

Standard: DIN 875

Calibration: F1

Right angle tolerance: 0.035 mm

Shank cross-section: 25×5 mm

Technical description

Shank cross-section	25×5 mm
Right angle tolerance	0.035 mm
Stock length	150×100 mm
Calibration	F1

Standard	DIN 875
Accuracy	2
Type of product	Try squares

Services

Calibration Stock, try, and bevel edge squares maximum arm length 300 mm	015020 300
Labelling laser-etched Type	018940
DAkkS calibration Stock, try, and bevel edge squares maximum arm length 750 mm	015600 750
DAkkS calibration Stock, try, and bevel edge squares maximum arm length 750 mm	025010 750
Recalibration Stock, try, and bevel edge squares maximum arm length 300 mm	025000 300

Accessories

Wooden case for stock length 150X100 mm	451600 150X100
---	----------------