



## Try square Accuracy class 2, Stock length: 100X70mm



### Order data

Order number	452600 100X70
GTIN	4045197205773
Item class	42F

### Description

**Version:**

All faces and edges ground. Inspection test faces ground.

**Application:**

For accurate general workshop work.

**Accuracy:**

**DIN 875 / 2** – angle tolerance e.g. for size 100×70 = 0.030 mm.

Standard: DIN 875

Calibration: F1

Right angle tolerance: 0.03 mm

Shank cross-section: 20×5 mm

### Technical description

Shank cross-section	20×5 mm
Right angle tolerance	0.03 mm
Stock length	100×70 mm
Calibration	F1

Standard	DIN 875
Accuracy	2
Type of product	Try squares

## Services

Calibration Stock, try, and bevel edge squares maximum arm length 100 mm	015020 100
Labelling laser-etched Type	018940
DAkkS calibration Stock, try, and bevel edge squares maximum arm length 750 mm	015600 750
Recalibration Stock, try, and bevel edge squares maximum arm length 100 mm	025000 100
DAkkS calibration Stock, try, and bevel edge squares maximum arm length 750 mm	025010 750

## Accessories

Wooden case for stock length 100X70 mm	451600 100X70
--	---------------