



Vertical toggle clamp with horizontal base, Type: 3



Order data

Order number	376508 3
GTIN	4045197226280
Item class	32S

Description

Version:

With horizontal base for fixing to base plates etc.

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Hole spacing e: 19 mm

Hole spacing f: 31.6 mm

Bore \varnothing d: 7.2 mm

Clamping height H: 32 mm

Clamping force P1: 1800 N

Clamping force P2: 2500 N

Technical description

overall length	90 mm
Hole spacing f	31.6 mm

Bore Ø d	7.2 mm
Hole spacing e	19 mm
Contact screw	M8×45 mm
Clamping force P1	1800 N
Clamping force P2	2500 N
overall height	205 mm
Type	376508 3
Clamping height H	32 mm
Type of product	Vertical toggle clamps