



Horizontal toggle clamp with horizontal base, Type: 1



Order data

Order number	376625 1
GTIN	4045197229915
Item class	32S

Description

Version:

Captive contact screws.

With horizontal base for fixing to base plates etc.

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Hole spacing e: 13.5 mm

Hole spacing f: 19.7 mm

Bore Ø d: 5.2 mm

Clamping height H: 18 mm

Clamping force P1: 460 N

Clamping force P2: 700 N

Technical description

Hole spacing f	19.7 mm
Hole spacing e	13.5 mm
overall height	38 mm
Clamping force P1	460 N
Clamping force P2	700 N

overall length	105 mm
Bore Ø d	5.2 mm
Contact screw	M5×30 mm
Type	376625 1
Clamping height H	18 mm
Type of product	Horizontal toggle clamp