



Vertical toggle clamp with horizontal base, Type: 1



Order data

Order number	376508 1
GTIN	4045197226266
Item class	32S

Description

Version:

With horizontal base for fixing to base plates etc.

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Hole spacing e: 16 mm

Hole spacing f: 24 mm

Bore Ø d: 3 mm

Clamping height H: 19 mm

Clamping force P1: 500 N

Clamping force P2: 710 N

Technical description

Hole spacing e	16 mm
overall length	51.5 mm

Clamping force P1	500 N
Clamping force P2	710 N
Bore Ø d	3 mm
overall height	77 mm
Hole spacing f	24 mm
Contact screw	M5×30 mm
Type	376508 1
Clamping height H	19 mm
Type of product	Vertical toggle clamps